


# Thermo Scientific Masterflex I/P

## Multichannel, Washdown Pumps



Masterflex® I/P® Series



- Convenient three- and four-channel fixed-speed pumps come complete with Pump Heads, tubing, and drive.
- Use multiple channels to increase your flow rate, or pump different fluids simultaneously from a single drive.
- Accept any Masterflex tubing formulation—configure for a broad range of applications, including pumping multiple lines of inks, chemicals, and pharmaceuticals.
- Fluid never contacts the pump, so clean up is quick and easy — simply replace the tubing!
- Change flow rate by changing tubing size.
- Easy-to-clean, IP55-rated housing—simply hose down after use.
- Combination on/off/reverse switch—purge before or after pumping; pump fluid in either direction.

**Holland**<sup>®</sup>  
**APPLIED TECHNOLOGIES**  
Indianapolis • Chicago • San Juan  
[www.hollandapt.com](http://www.hollandapt.com)  
800-800-8464



ISO9001:2000  
SUPPLIER CERTIFIED

2  
year  
warranty

I/P 15 9/1/09

### Flow rates, LPM (GPM)

Motor rpm	Masterflex I/P precision tubing sizes		
	I/P 26	I/P 73	I/P 82
180	1.1 (0.3)	2.3 (0.6)	3.7 (1.0)

### Specifications & Ordering Information

Catalog number	950-3613	950-3014
Included Pump Head	Easy-Load®	
Number of channels/Pump Heads	3	4
rpm	180 (with included NEMA adapter)	
Voltage	115 V AC, 50/60 Hz	115 V AC, 60 Hz
Speed regulation	±1% (with constant line voltage)	
IP rating	IP55	
Agency approvals	UL, cUL, CE	
Shipping weight	30 kg (66 lb)	

  
**Holland®**  
**APPLIED TECHNOLOGIES**  
Indianapolis • Chicago • San Juan  
[www.hollandapt.com](http://www.hollandapt.com)  
800-800-8464

[www.thermo.com/fluidhandling](http://www.thermo.com/fluidhandling)

Barrington, IL 60010  
1-800-637-3739  
1-847-381-7050  
1-847-381-7053 fax

I/P 16 9/1/09

**Thermo**  
SCIENTIFIC